

V71.17.17Z

Release Date: 10 December 2018

This firmware release includes features of the previous release. It is for use with the following printer models:

- GK888d
- GK888t
- GC420D-EPL
- GC420D-ZPL
- GC420T-EPL
- GC420T-ZPL

Changes

Improved printhead support.

V71.17.15Z

Release Date: 13 June 2013

This firmware release includes features of the previous release. It is for use with the following printer models:

- GK888d
- GK888t
- GC420D-EPL
- GC420D-ZPL
- GC420T-EPL
- GC420T-ZPL

Issues Corrected

- Calibration of small height labels has been enhanced.
- The printer will now report "12" when there is a label ready to be removed and the unit is in peel mode.
- Improved vertical registration when in "device.epl_legacy_mode" "registration" mode.
- Handling of functions within GS128 barcodes has been improved.
- Positioning of human readable text in EPL barcodes improved when the height of the barcode is larger than the length of the label.
- The printer will now use the ZPL Font 0 as the default font.
- Print positioning when the JB command is used has been improved.
- Code 128 landscape printing improved to correct image artifact issue.
- Nine digit zip codes are now correctly supported in EPL-formatted Maxicode barcodes.

- When in EPL mode the R command now accepts negative values.
- Enhanced memory management to resolve text field not printing issue.
- Using embedded commands in a Field Block (^FB) field are now correctly supported.
- Improved interaction between the q and R commands
- The reporting for "Number of formats in the Receive buffer" has been corrected.

Changes

- Support for EPL1
- The SGD commands "device.epl_legacy_mode" now support the "print orientation" parameter.

V71.17.14Z

Release Date: 01 October 2012

This firmware release includes features of the previous release. It is for use with the following printer models:

- GK888d
- GK888t
- GC420D-EPL
- GC420D-ZPL
- GC420T-EPL
- GC420T-ZPL

Issues Corrected

The printer now supports a broader range of PC RS232 serial port power up sequence behaviors.

Changes

Line mode, in continuous mode only, is now supported on 203 DPI Direct Thermal units.

V71.17.13Z

Release Date: 30 March 2012

This firmware release includes features of the previous release. It is for use with the following printer models:

- GK888d
- GK888t
- GC420D-EPL
- GC420D-ZPL
- GC420T-EPL
- GC420T-ZPL

Issues Corrected

The printer now supports a broader range of PC RS232 serial port power up sequence behavior.

V71.17.12Z

Release Date: 6 February 2012

This firmware release includes features of the previous release. It is for use with the following printer models:

- GK888d
- GK888t
- GC420D-EPL
- GC420D-ZPL
- GC420T-EPL
- GC420T-ZPL

Issues Corrected

The Plug and Play string in this firmware now defaults to EPL.

Changes

This firmware now supports the GC420D-EPL, GC420D-ZPL, GC420T-EPL, and GC420T-ZPL models.

V71.17.11Z

Release Date: 6 January 2011

This is the initial release of this firmware. It is for use with the following printer models:

- GK888d
- GK888